



WBHWSV2

Allure 2 Gang IP44 Plate Vert

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour

Colour	White
--------	-------

Identification

Assembly arrangement

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons

Number of buttons	2
-------------------	---

Dimensions

Dimensions

Dimensions	117 x 77 mm
------------	-------------

Electric current

Rated current

Rated current	16 A
---------------	------

Texts

Installation mode	For screw fastening
-------------------	---------------------

Type of connection	With screw terminals
--------------------	----------------------

Lighting	Without lighting (cannot be illuminated)
----------	--

Switch mode	2-way, with loop terminal
-------------	---------------------------

Sustainability

REACH-SVHC free

REACH-SVHC free	Yes
-----------------	-----

RoHS conform

RoHS conform	Yes
--------------	-----