

**fuse switch disconnecter D02 1P+N 63A**

**Technical Features**

**Fuse**

Fuse size	D02
-----------	-----

**Architecture**

Number of poles	3
-----------------	---

**Electric current**

Rated current	63 A
Rated current of fuse cartridge	0.5 A 1 A 2 A 6 A 10 A 16 A 20 A 25 A 35 A 50 A 63 A

**Installation, mounting**

Mounting on	DIN rail
-------------	----------

**Dimensions**

Height	90 mm
Width	71 mm

**Connection**

Cross-section flexible conductor	35 mm <sup>2</sup> max.
----------------------------------	-------------------------

**Use conditions**

Operating temperature	-25 - 55 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Power**

Total power loss under IN	5.50 W
---------------------------	--------

**Connection**

Cross-section rigid conductor	35 mm <sup>2</sup>
-------------------------------	--------------------

**Materials**

Material	Plastic
----------	---------