

fuse switch disconnecter D02 3P 63A

Technical Features

Fuse

Fuse size	D02
-----------	-----

Architecture

Number of poles	3
-----------------	---

Electric current

Rated current	63 A
Rated current of fuse cartridge	0.5 A 1 A 2 A 6 A 10 A 16 A 20 A 25 A 35 A 50 A 63 A

Installation, mounting

Mounting on	DIN rail
-------------	----------

Dimensions

Height	90 mm
Width	80 mm

Connection

Cross-section flexible conductor	35 mm ² max.
----------------------------------	-------------------------

Use conditions

Operating temperature	-25 - 55 °C
-----------------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Power

Total power loss under IN	5.50 W
---------------------------	--------

Connection

Cross-section rigid conductor	35 mm ²
-------------------------------	--------------------

Materials

Material	Plastic
----------	---------