Product Datasheet
WBHSA2-MW



WBHSA2-MW

Allure Architrave 2 gang MW

Technical Features

Installation, mounting

Mounting on	Flush mounting

Voltage

Rated voltage	250 V

Frequency

Frequency	50 - 50 Hz

Materials

Colour	White

Identification

Assembly arrangement	Basic element with full cover plate

Connectivity

Mounting type	Screw mounting

Controls and indicators

Number of buttons	2

Electric current

Rated current IN	16 A

Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Push button	No

Sustainability

Halogen free	Yes
REACh-SVHC free	Yes
RoHS conform	Yes