



WBHP1R-MW

Allure Single GPO 10A with round Earth MW

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
--------	-------

Installation, mounting

Mounting on	Surface mounting
Mounting-/Connection Position	Horizontal

Connectivity

Mounting type	Screw mounting
---------------	----------------

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Complete housing

Suitable for

allure	
--------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes