



WBHP1R-MW

**Allure Single GPO 10A with round Earth MW**

**Technical Features**

**Electric current**

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

**Materials**

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

**Installation, mounting**

|                               |                  |
|-------------------------------|------------------|
| Mounting on                   | Surface mounting |
| Mounting-/Connection Position | Horizontal       |

**Connectivity**

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

**Equipment**

|                                   |                                 |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert            | No                              |
| With hinged lid                   | No                              |

**Accessories**

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

**Safety**

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

**Texts**

|       |                  |
|-------|------------------|
| Cover | Complete housing |
|-------|------------------|

**Suitable for**

|        |  |
|--------|--|
| allure |  |
|--------|--|

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |