



WBHP1R-MW

### Allure Single GPO 10A with round Earth MW

#### Technical Features

##### Electric current

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

##### Voltage

|                 |             |
|-----------------|-------------|
| Nominal voltage | 250 - 250 V |
|-----------------|-------------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

##### Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

##### Installation, mounting

|                               |                  |
|-------------------------------|------------------|
| Mounting on                   | Surface mounting |
| Mounting-/Connection Position | Horizontal       |

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Equipment

|                                   |                                 |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert            | No                              |
| With hinged lid                   | No                              |

##### Accessories

|                     |    |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

##### Capacity

|                   |   |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

##### Functions

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting    | No |

##### Texts

|         |                  |
|---------|------------------|
| Imprint | Without imprint  |
| Cover   | Complete housing |

##### Suitable for

|        |  |
|--------|--|
| allure |  |
|--------|--|

##### Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |