



WBHSV1

### Allure 1 Gang Switch Plate cw mechs

#### Technical Features

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

##### Materials

|                |                    |
|----------------|--------------------|
| Colour         | White              |
| Surface finish | Glossy             |
| Material       | Polycarbonate (PC) |
| Treatment      | Untreated          |

##### Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

##### Dimensions

|                                    |       |
|------------------------------------|-------|
| Built-in depth                     | 15 mm |
| Built-in depth flush-mounted boxes | 15 mm |

##### Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP2X |
| Impact resistance IK          | IK08 |

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Texts

|                    |                                          |
|--------------------|------------------------------------------|
| Installation mode  | For screw fastening                      |
| Type of connection | With screw terminals                     |
| Lighting           | Without lighting (cannot be illuminated) |
| Switch mode        | 2-way, with loop terminal                |

##### Sustainability

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |