



WBHSV3

Allure 3 Gang Switch Plate cw mechs

Technical Features

Installation, mounting

Mounting on Flush mounting

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

Identification

Assembly arrangement Basic element with full cover plate

Connectivity

Mounting type Screw mounting

Controls and indicators

Number of buttons 3

Dimensions

Built-in depth 15 mm

Built-in depth flush-mounted boxes 15 mm

Safety

Ingress Protection (IP) class IP2X

Impact resistance IK IK08

Electric current

Rated current 16 A

Texts

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal

Sustainability

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes