



WBHSV2

Allure 2 Gang Switch Plate cw mechs

Technical Features

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	2
-------------------	---

Dimensions

Built-in depth	15 mm
Built-in depth flush-mounted boxes	15 mm

Safety

Ingress Protection (IP) class	IP2X
Impact resistance IK	IK08

Electric current

Rated current	16 A
---------------	------

Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way, with loop terminal

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes