



WBHP2XS

**Allure DGPO 10A with Extra Switch**

**Technical Features**

**Electric current**

|               |      |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

**Frequency**

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

**Materials**

|                |                                     |
|----------------|-------------------------------------|
| Colour         | White                               |
| Surface finish | Glossy                              |
| Material       | Polycarbonate (PC)<br>Thermoplastic |
| Treatment      | Untreated                           |

**Dimensions**

|                                    |         |
|------------------------------------|---------|
| Height                             | 82 mm   |
| Width                              | 120 mm  |
| Depth                              | 9,50 mm |
| Number of units                    | 1       |
| Built-in depth flush-mounted boxes | 20 mm   |

**Installation, mounting**

|                               |                |
|-------------------------------|----------------|
| Mounting on                   | Flush mounting |
| Mounting-/Connection Position | Horizontal     |

**Connectivity**

|                    |                |
|--------------------|----------------|
| Type of connection | Screw terminal |
| Mounting type      | Screw mounting |

**Equipment**

|                                   |                                 |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert            | No                              |
| With hinged lid                   | No                              |
| With round protective earth pin   | No                              |
| With signal lamp                  | No                              |

**Capacity**

|                   |   |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

**Safety**

|                               |      |
|-------------------------------|------|
| Impact resistance IK          | IK08 |
| Ingress Protection (IP) class | IP2X |

**Functions**

|                           |    |
|---------------------------|----|
| With orientation lighting | No |
|---------------------------|----|

**Identification**

|              |    |
|--------------|----|
| With imprint | No |
|--------------|----|

**Texts**

|                    |                                     |
|--------------------|-------------------------------------|
| Cover              | Full cover plate                    |
| Protection         | Without enhanced contact protection |
| Type of connection | With screw terminals                |

**Suitable for**

|        |  |
|--------|--|
| allure |  |
|--------|--|

---

**Sustainability**

|                 |     |
|-----------------|-----|
| Halogen free    | Yes |
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |