



WBHP2XS

Allure DGPO 10A with Extra Switch

Technical Features

Electric current

Rated current 10 A

Frequency

Frequency 50 - 50 Hz

Materials

Colour White

Surface finish Glossy

Material Polycarbonate (PC)
Thermoplastic

Treatment Untreated

Dimensions

Height 82 mm

Width 120 mm

Depth 9,50 mm

Number of units 1

Built-in depth flush-mounted boxes 20 mm

Installation, mounting

Mounting on Flush mounting

Mounting-/Connection Position Horizontal

Connectivity

Type of connection Screw terminal

Mounting type Screw mounting

Equipment

Connector/plug type socket outlet Australian standard AS/NZS 3112

Rotated central insert No

With hinged lid No

With round protective earth pin No

With signal lamp No

Capacity

Number of modules 2

Safety

Impact resistance IK IK08

Ingress Protection (IP) class IP2X

Functions

With orientation lighting No

Identification

With imprint No

Texts

Cover Full cover plate

Protection Without enhanced contact protection

Type of connection With screw terminals

Suitable for

allure

Sustainability

| | |
|-----------------|-----|
| Halogen free | Yes |
| REACH-SVHC free | Yes |
| RoHS conform | Yes |