



VML\_SIZE\_5

**10 Way HI Integrity Configurable 100A Switch 2\*100A 30mA RCCB Round KO**

**Technical Features**

**Installation, mounting**

Mounting on	Surface mounting
-------------	------------------

**Functions**

Has protection main switch	Yes
Overvoltage protection	No

**Configuration**

Number of arc fault detection devices AFDD	0
--	---

**Capacity**

Number of modules	10
-------------------	----

**Electric current**

Rated current	100 A
---------------	-------

**Dimensions**

Depth	100 mm
Height	245 mm
Width	368.40 mm

**Cover, door**

Interlockable	No
Door/cover is transparent	No

**Materials**

Colour	Pure white
Material	Steel

**Connection**

Number of accessible phases	2
-----------------------------	---

**Scope of delivery**

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

**Equipment**

With energy meter	No
-------------------	----

**Safety**

Ingress Protection (IP) class	IP2XC
-------------------------------	-------

**Sustainability**

RoHS conform	Yes
--------------	-----