



WBMTPB

6A 240V PB Momentary mech

Technical Features

Electric current

Switching current	6 A
-------------------	-----

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Voltage

Rated voltage	250 V
---------------	-------

Frequency

Frequency	0-50 Hz
-----------	---------

Materials

Colour	White
RAL code	9010
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Basic element with central cover plate
----------------------	--

Connectivity

Mounting type	Snap-in mounting
With claw mounting	No

Controls and indicators

Number of buttons	1
-------------------	---

Dimensions

Dimensions	27 x 23.5 mm
Built-in depth	27 mm
Diameter	23.5 mm

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Electric current

Rated current	6 A
---------------	-----

Connection

Type of contacts	1NC+1NO
Connector/plug type	RotoLoc®

Texts

Installation mode	RotoLoc®
Type of connection	With screw terminals
Lighting	Can be illuminated by LED illuminating cartridge
Switch mode	Change-over contact, usable as NC or NO

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes