



WBMTPB

**6A 240V PB Momentary mech**

**Technical Features**

**Electric current**

Switching current 6 A

**Installation, mounting**

Mounting on Flush mounting

**Voltage**

Rated voltage 250 V

**Frequency**

Frequency 0-50 Hz

**Materials**

Colour White

RAL code 9010

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

**Identification**

Assembly arrangement Basic element with central cover plate

**Connectivity**

Mounting type Snap-in mounting

With claw mounting No

**Controls and indicators**

Number of buttons 1

**Dimensions**

Dimensions 27 x 23.5 mm

Built-in depth 27 mm

Diameter 23.5 mm

**Safety**

Ingress Protection (IP) class IP20

**Architecture**

Control/operation element Single push button

**Electric current**

Rated current 6 A

**Connection**

Type of contacts 1NC+1NO

Connector/plug type RotoLoc®

**Texts**

Installation mode RotoLoc®

Type of connection With screw terminals

Lighting Can be illuminated by LED illuminating cartridge

Switch mode Change-over contact, usable as NC or NO

**Sustainability**

Halogen free Yes

REACH-SVHC free Yes

RoHS conform Yes