



WBHP2S

Allure Double GPO

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Rated voltage	250 V
Nominal voltage	230 - 250 V
Output voltage	230-250 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
RAL code	9010
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Depth	18 mm
Number of units	2
Built-in depth flush-mounted boxes	18 mm

Connection

Connector/plug type	Terminal
---------------------	----------

Installation, mounting

Mounting on	Wall mounting Flush mounting Surface-mounted installation box Surface-mounted frame
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	2x 2 socket outlets

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP2X

Functions

With orientation lighting	No
With function lighting	No

Identification		
With imprint		Yes
Texts		
Imprint		Without imprint
Cover		Full cover plate
Lighting		Without neon lamp
Wiring		With earth connection
Protection		Without enhanced contact protection
Type of connection		With screw terminals
Suitable for		
allure		
Sustainability		
REACH-SVHC free		Yes
RoHS conform		Yes