



WBHP2S

Allure Double GPO

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Rated current	10 A
---------------	------

Voltage

Output voltage	230-250 V
----------------	-----------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
RAL code	9010
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Dimensions

Depth	18 mm
Number of units	2
Built-in depth flush-mounted boxes	18 mm

Connection

Connector/plug type	Terminal
---------------------	----------

Installation, mounting

Mounting on	Wall mounting Flush mounting Surface-mounted installation box Surface-mounted frame
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Plug-in connection
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	2x 2 socket outlets

Capacity

Number of modules	2
-------------------	---

Safety

With enhanced contact protection	Yes
Impact resistance IK	IK07
Ingress Protection (IP) class	IP2X

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Full cover plate
-------	------------------

Lighting	Without neon lamp
----------	-------------------

Wiring	With earth connection
--------	-----------------------

Protection	Without enhanced contact protection
------------	-------------------------------------

Type of connection	With screw terminals
--------------------	----------------------

Terminal	With mains connection terminals
----------	---------------------------------

Suitable for

allure	
--------	--

Sustainability

REACH-SVHC free	Yes
-----------------	-----

RoHS conform	Yes
--------------	-----
