



VB10101TSPD

### Vega 4Row 7W 1RCD - 2x6A Ltg. RCBOs SPD

#### Technical Features

##### Installation, mounting

|             |                  |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

##### Functions

|                            |     |
|----------------------------|-----|
| Has protection main switch | No  |
| Overvoltage protection     | Yes |

##### Configuration

|                                            |   |
|--------------------------------------------|---|
| Number of arc fault detection devices AFDD | 0 |
|--------------------------------------------|---|

##### Capacity

|                   |    |
|-------------------|----|
| Number of modules | 72 |
|-------------------|----|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

##### Dimensions

|                       |         |
|-----------------------|---------|
| Depth                 | 145 mm  |
| Height                | 750 mm  |
| Width                 | 370 mm  |
| Number of width units | 18      |
| Thickness of sidewall | 2.50 mm |

##### Cover, door

|                           |     |
|---------------------------|-----|
| Interlockable             | Yes |
| Door/cover is transparent | Yes |

##### Materials

|          |                  |
|----------|------------------|
| RAL code | 9010             |
| Colour   | Pure white       |
| Material | Polystyrene (PS) |

##### Installation, mounting

|                            |    |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

##### Connection

|                             |   |
|-----------------------------|---|
| Number of accessible phases | 1 |
|-----------------------------|---|

##### Scope of delivery

|                                                |   |
|------------------------------------------------|---|
| Number of earth leakage circuit breaker type A | 3 |
| Number of RCCB in enclosure                    | 1 |

##### Equipment

|                        |     |
|------------------------|-----|
| Number of light groups | 2   |
| Number of rows         | 4   |
| With energy meter      | No  |
| Number of rails        | 4   |
| Extension possible     | Yes |
| With bell transformer  | No  |

##### Safety

|                               |      |
|-------------------------------|------|
| Impact resistance IK          | IK07 |
| Ingress Protection (IP) class | IP40 |

##### Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|