



WBHP120

**Allure Single GPO 20A**

**Technical Features**

**Electric current**

Rated current	20 A
---------------	------

**Voltage**

Nominal voltage	250 - 250 V
-----------------	-------------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	White
--------	-------

**Dimensions**

Height	77 mm
Width	117 mm

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
Mounting type	Screw mounting

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Functions**

With orientation lighting	No
With function lighting	No

**Texts**

Imprint	Without imprint
Cover	Full cover plate
Type of connection	With screw terminals

**Suitable for**

allure	
--------	--

**Sustainability**

REACH-SVHC free	Yes
RoHS conform	Yes