



WBHP120

### Allure Single GPO 20A

#### Technical Features

##### Electric current

Rated current	20 A
---------------	------

##### Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

##### Frequency

Frequency	50 - 50 Hz
-----------	------------

##### Materials

Colour	White
--------	-------

##### Dimensions

Height	77 mm
Width	117 mm

##### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

##### Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

##### Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

##### Accessories

Has labelling field	No
---------------------	----

##### Capacity

Number of modules	1
-------------------	---

##### Functions

With orientation lighting	No
With function lighting	No

##### Texts

Imprint	Without imprint
Cover	Full cover plate
Type of connection	With screw terminals

##### Suitable for

allure	
--------	--

##### Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes