



VBE88101PSPD

Vega,2Row,5/8 WAY SPLIT LOAD CU,P/DOOR,2P ISOLATOR,SPD,1xRCD,2x6A LIGHTING RCBOs

Technical Features

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Functions

| | |
|----------------------------|----|
| Has protection main switch | No |
|----------------------------|----|

| | |
|------------------------|-----|
| Overvoltage protection | Yes |
|------------------------|-----|

Configuration

| | |
|--|---|
| Number of arc fault detection devices AFDD | 0 |
|--|---|

Capacity

| | |
|-------------------|----|
| Number of modules | 36 |
|-------------------|----|

Electric current

| | |
|---------------|------|
| Rated current | 80 A |
|---------------|------|

Dimensions

| | |
|-------|--------|
| Depth | 145 mm |
|-------|--------|

| | |
|--------|--------|
| Height | 450 mm |
|--------|--------|

| | |
|-------|--------|
| Width | 370 mm |
|-------|--------|

| | |
|-----------------------|----|
| Number of width units | 18 |
|-----------------------|----|

| | |
|-----------------------|---------|
| Thickness of sidewall | 2.50 mm |
|-----------------------|---------|

Cover, door

| | |
|---------------|-----|
| Interlockable | Yes |
|---------------|-----|

| | |
|---------------------------|-----|
| Door/cover is transparent | Yes |
|---------------------------|-----|

Materials

| | |
|----------|------|
| RAL code | 9010 |
|----------|------|

| | |
|--------|------------|
| Colour | Pure white |
|--------|------------|

| | |
|----------|------------------|
| Material | Polystyrene (PS) |
|----------|------------------|

Installation, mounting

| | |
|----------------------------|----|
| Suitable for outdoor usage | No |
|----------------------------|----|

Connection

| | |
|-----------------------------|---|
| Number of accessible phases | 1 |
|-----------------------------|---|

Scope of delivery

| | |
|--|---|
| Number of earth leakage circuit breaker type A | 3 |
|--|---|

| | |
|-----------------------------|---|
| Number of RCCB in enclosure | 1 |
|-----------------------------|---|

Equipment

| | |
|------------------------|---|
| Number of light groups | 2 |
|------------------------|---|

| | |
|----------------|---|
| Number of rows | 2 |
|----------------|---|

| | |
|-------------------|----|
| With energy meter | No |
|-------------------|----|

| | |
|-----------------|---|
| Number of rails | 2 |
|-----------------|---|

| | |
|-----------------------|----|
| With bell transformer | No |
|-----------------------|----|

Safety

| | |
|----------------------|------|
| Impact resistance IK | IK07 |
|----------------------|------|

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP40 |
|-------------------------------|------|

| | |
|------------------|--------------------|
| Protection class | Isolation class II |
|------------------|--------------------|

Sustainability

| | |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|