



TRM692AU



### Flush mounted output 3A for shutters or blinds + 2 inputs

#### Technical Features

##### Connectivity

Radio protocol	KNX Radio
Receiver category	2
With bus system KNX	No
With bus system KNX radio	Yes

##### Dimensions

Height	27 mm
Built-in depth	40 mm

##### Electric current

Rated current	3 A
---------------	-----

##### Materials

Colour	Light grey
--------	------------

##### Equipment

Radio frequency bidirectional	Yes
With switch for manual switch	Yes

##### Frequency

Frequency	50 - 50 Hz
Radio reception frequency	433 - 433 MHz

##### Power

Output power	690 W
--------------	-------

##### Voltage

Operating voltage	230 - 230 V
Rated operational voltage U <sub>e</sub>	230 - 230 V
System supply voltage	230 V AC

##### Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

##### Use conditions

Operating temperature	-10 - 50 °C
-----------------------	-------------

##### Connection

Cross-section rigid conductor	0.5 - 2.5 mm <sup>2</sup>
Cross-section flexible conductor	0.5 - 1.5 mm <sup>2</sup>

##### Texts

Function	Reset function (to factory setting)
Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

##### Sustainability

RoHS conform	Yes
--------------	-----