



WBHCKSV1

Allure Cooker switch 40A DP Vert

Technical Features

Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 1 |
|-------------------|---|

Electric current

|               |      |
|---------------|------|
| Rated current | 40 A |
|---------------|------|

Texts

|                    |                                          |
|--------------------|------------------------------------------|
| Installation mode  | For screw fastening                      |
| Type of connection | With screw terminals                     |
| Lighting           | Without lighting (cannot be illuminated) |
| Switch mode        | 2-pole off                               |

Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform    | Yes |