



LF325PV

**PV Fuse-link 10x38 mm 600V DC 25A**

**Technical Features**

**Fuse**

Fuse characteristics	gPV
Fuse size	10.3 x 38

**Electric current**

Rated current	25 A
---------------	------

**Power**

Total power loss under I <sub>N</sub>	2.74 W
---------------------------------------	--------

**Main electrical attributes**

Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1	30 kA
---	-------

**Voltage**

Type voltage supply	DC
Nominal voltage	600 - 600 V

**Architecture**

Curve	C
-------	---

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes