



WBHWSH2

#### Allure 2 Gang IP44 Plate Horiz

##### Technical Features

##### Installation, mounting

|             |                |
|-------------|----------------|
| Mounting on | Flush mounting |
|-------------|----------------|

##### Frequency

|           |            |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

##### Materials

|        |       |
|--------|-------|
| Colour | White |
|--------|-------|

##### Identification

|                      |                                     |
|----------------------|-------------------------------------|
| Assembly arrangement | Basic element with full cover plate |
|----------------------|-------------------------------------|

##### Connectivity

|               |                |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

##### Controls and indicators

|                   |   |
|-------------------|---|
| Number of buttons | 2 |
|-------------------|---|

##### Dimensions

|            |             |
|------------|-------------|
| Dimensions | 77 x 117 mm |
|------------|-------------|

##### Electric current

|               |      |
|---------------|------|
| Rated current | 16 A |
|---------------|------|

##### Texts

|                   |                     |
|-------------------|---------------------|
| Installation mode | For screw fastening |
|-------------------|---------------------|

|                    |                      |
|--------------------|----------------------|
| Type of connection | With screw terminals |
|--------------------|----------------------|

|          |  |
|----------|--|
| Lighting | Without lighting (cannot be illuminated) |
|----------|--|

|             |                           |
|-------------|---------------------------|
| Switch mode | 2-way, with loop terminal |
|-------------|---------------------------|

##### Sustainability

|                 |     |
|-----------------|-----|
| REACH-SVHC free | Yes |
|-----------------|-----|

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|