



VML\_SIZE\_4

### 6 Way 3+3 80A Switch 2\*80A 30mA Type A 80A InA

#### Technical Features

##### Installation, mounting

Mounting on	Surface mounting
-------------	------------------

##### Functions

Has protection main switch	Yes
Overvoltage protection	Yes

##### Configuration

Number of arc fault detection devices AFDD	0
--	---

##### Capacity

Number of modules	6
-------------------	---

##### Electric current

Rated current	100 A
---------------	-------

##### Dimensions

Depth	100 mm
Height	246 mm
Width	299 mm
Thickness of sidewall	1 mm

##### Cover, door

Interlockable	No
Door/cover is transparent	No

##### Materials

RAL code	9010
Colour	Pure white
Material	Steel

##### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

##### Connection

Number of accessible phases	1
-----------------------------	---

##### Scope of delivery

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

##### Equipment

Number of rows	1
With energy meter	No
Extension possible	No
With bell transformer	No

##### Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC