



VML_SIZE_4

6 Way 3+3 80A Switch 2*80A 30mA Type A 80A InA

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	Yes
Overvoltage protection	Yes

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	6
-------------------	---

Electric current

Rated current	100 A
---------------	-------

Dimensions

Depth	100 mm
Height	246 mm
Width	299 mm
Thickness of sidewall	1 mm

Cover, door

Interlockable	No
Door/cover is transparent	No

Materials

RAL code	9010
Colour	Pure white
Material	Steel

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	2
Number of RCCB in enclosure	2

Equipment

Number of rows	1
With energy meter	No
Extension possible	No
With bell transformer	No
With socket outlet	No

Safety

Impact resistance IK	IK05
Ingress Protection (IP) class	IP2XC

Sustainability

RoHS conform	Yes
--------------	-----