



VB10101PSPD

Vega 4Row 7W 1RCD - 2x6A Ltg. RCBOs SPD

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	No
Overvoltage protection	Yes

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	72
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth	145 mm
Height	750 mm
Width	370 mm
Number of width units	18
Thickness of sidewall	2.50 mm

Cover, door

Interlockable	Yes
Door/cover is transparent	Yes

Materials

RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	3
Number of RCCB in enclosure	1

Equipment

Number of light groups	2
Number of rows	4
With energy meter	No
Number of rails	4
Extension possible	Yes
With bell transformer	No

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40

Sustainability

RoHS conform	Yes
--------------	-----