



WBHP2S-MW

Allure Double GPO Matt White

Technical Features

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
Surface finish	Matt
Material	Polycarbonate (PC) Thermoplastic
Treatment	Varnished

Dimensions

Number of units	2
Built-in depth flush-mounted boxes	18 mm

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Texts

Cover	Full cover plate
Protection	Without enhanced contact protection
Type of connection	With screw terminals

Suitable for

allure	
--------	--

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes