



WBHP2S-MB

Allure Double GPO Matt Black

Technical Features

Electric current

Rated current	10 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	Black
Surface finish	Matt
Material	Polycarbonate (PC) Thermoplastic
Treatment	Untreated

Dimensions

Height	81 mm
Width	119 mm
Depth	25 mm
Number of units	2

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Horizontal

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	2
-------------------	---

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Full cover plate
Protection	Without enhanced contact protection
Type of connection	With screw terminals

Suitable for

allure	
--------	--

Sustainability	
RoHS conform	Yes