



LF315PV

**PV Fuse-link 10x38 mm 1000V DC 15A**

**Technical Features**

**Fuse**

|                      |           |
|----------------------|-----------|
| Fuse characteristics | gPV       |
| Fuse size            | 10.3 x 38 |

**Electric current**

|               |      |
|---------------|------|
| Rated current | 15 A |
|---------------|------|

**Power**

|                                       |        |
|---------------------------------------|--------|
| Total power loss under I <sub>N</sub> | 2.44 W |
|---------------------------------------|--------|

**Main electrical attributes**

|                                                                                   |       |
|-----------------------------------------------------------------------------------|-------|
| Rated short-circuit breaking capacity I <sub>cn</sub> AC according to IEC 60898-1 | 30 kA |
|-----------------------------------------------------------------------------------|-------|

**Voltage**

|                     |               |
|---------------------|---------------|
| Type voltage supply | DC            |
| Nominal voltage     | 1000 - 1000 V |

**Architecture**

|       |   |
|-------|---|
| Curve | C |
|-------|---|