



SPB140R

Surge Protection Device 1P T2 TNC Uc 275V In 20kA I_{max} 40kA remote contact

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U _e	240 - 415 V
Continuous operating voltage U _c according to IEC 61643-1	275 V
Voltage protection level U _p according to IEC 61643-1	1.35 kV
Voltage protection level U _p L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level U _p L-N/PEN IEC 61643-11	1350 V

Electric current

Nominal discharge current I _n 8 - 20 μs L-N(PEN)/N-PE IEC 61643	20 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I _{max}) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	96.8 mm
Width	17.6 mm
Depth	58.20 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN TT
--------------	----------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes