



WGDS113SUSBKB

**13A SINGLE SWITCHED SOCKET + USB, KB**

**Technical Features**

**Voltage**

Rated voltage	230 V
---------------	-------

**Electric current**

Output current	2400 mA
Rated current	13 A

**Voltage**

Output voltage	0-0 V
----------------	-------

**Use conditions**

Operating temperature	-20 - 45 °C
-----------------------	-------------

**Frequency**

Frequency	50 - 60 Hz
-----------	------------

**Power**

Output power	0 W
Power consumption standby	0.15 W

**Materials**

Colour	Knight black
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Coated
Contains recycled material (% of total plastic weight)	0 %

**Dimensions**

Height	28 mm
Width	86 mm
Depth	28 mm

**Cable**

Cable length	0 m
--------------	-----

**Dimensions**

Built-in depth flush-mounted boxes	35 mm
Built-in depth	28 mm

**Connection**

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0.08 - 4 mm <sup>2</sup>
Number of conduit inlets	0

**Installation, mounting**

Mounting on	Flush mounting
Mounting-/Connection Position	Back

**Connectivity**

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	AA

**Equipment**

Connector/plug type socket outlet	British Standard
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	No

---

**Equipment**

With signal lamp	No
With lock	No

**Accessories**

Has labelling field	No
Pre-equipped with	None

**Capacity**

Number of modules	0
-------------------	---

**Safety**

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

**Functions**

With orientation lighting	No
With function lighting	No

**Identification**

With imprint	No
--------------	----

**Suitable for**

shark

**Sustainability**

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes