



VBE98101PSPD

Vega,3Row,5/8 WAY SPLIT LOAD CU,P/DOOR,2P ISOLATOR,1xRCD,2x6A LIGHTING RCBOs

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	No
----------------------------	----

Overvoltage protection	Yes
------------------------	-----

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	54
-------------------	----

Electric current

Rated current	80 A
---------------	------

Dimensions

Depth	145 mm
-------	--------

Height	600 mm
--------	--------

Width	370 mm
-------	--------

Number of width units	18
-----------------------	----

Thickness of sidewall	2.50 mm
-----------------------	---------

Cover, door

Interlockable	Yes
---------------	-----

Door/cover is transparent	Yes
---------------------------	-----

Materials

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Material	Polystyrene (PS)
----------	------------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	3
--	---

Number of RCCB in enclosure	1
-----------------------------	---

Equipment

Number of light groups	2
------------------------	---

Number of rows	3
----------------	---

With energy meter	No
-------------------	----

Number of rails	3
-----------------	---

With bell transformer	No
-----------------------	----

Safety

Impact resistance IK	IK07
----------------------	------

Ingress Protection (IP) class	IP40
-------------------------------	------

Protection class	Isolation class II
------------------	--------------------

Sustainability

RoHS conform	Yes
--------------	-----