



LF332M

Cylindrical fuse-links for industrial applications 10x38mm aM 32A 400V AC 120kA

Technical Features

Fuse

Fuse characteristics	aM
Fuse size	10.3 x 38

Electric current

Rated current	32 A
---------------	------

Power

Total power loss under IN	1.8 W
---------------------------	-------

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	120 kA
---	--------

Voltage

Type voltage supply	AC
Nominal voltage	400 - 400 V

Architecture

Curve	C
-------	---

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes