



SBE9102SPD

Gamma 3Row 7W 2RCD - 2x6A Ltg. MCBs SPD

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Functions

Has protection main switch	No
Overvoltage protection	Yes

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Configuration

Number of arc fault detection devices AFDD	0
--	---

Capacity

Number of modules	39
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth	103 mm
Height	500 mm
Width	250 mm
Number of width units	13
Thickness of sidewall	2.50 mm

Cover, door

Interlockable	Yes
Door/cover is transparent	Yes

Materials

RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)

Connection

Number of accessible phases	1
-----------------------------	---

Scope of delivery

Number of earth leakage circuit breaker type A	3
Number of RCCB in enclosure	1

Equipment

Number of light groups	2
Number of rows	3
With energy meter	No
Number of rails	3
With bell transformer	No
With socket outlet	No

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Protection class	Isolation class II
Number of earth leakage switches 300 mA	0