



LF325PV

PV Fuse-link 10x38 mm 600V DC 25A

Technical Features

Fuse

Fuse characteristics	gPV
Fuse size	10.3 x 38

Electric current

Rated current	25 A
---------------	------

Power

Total power loss under I _N	2.74 W
---------------------------------------	--------

Main electrical attributes

Rated short-circuit breaking capacity I _{cn} AC according to IEC 60898-1	30 kA
---	-------

Voltage

Type voltage supply	DC
Nominal voltage	600 - 600 V

Architecture

Curve	C
-------	---