



WGDEE1KB

Emergency switch;kb

Technical Features

Dimensions

|        |       |
|--------|-------|
| Width  | 86 mm |
| Height | 41 mm |
| Depth  | 41 mm |

Safety

|                               |      |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Voltage

|                 |         |
|-----------------|---------|
| Nominal voltage | 0-230 V |
|-----------------|---------|

Equipment

|                       |   |
|-----------------------|---|
| Number of NC contacts | 0 |
| Number of NO contacts | 0 |

Use conditions

|                       |            |
|-----------------------|------------|
| Operating temperature | -5 - 45 °C |
|-----------------------|------------|

Materials

|          |                    |
|----------|--------------------|
| Material | Polycarbonate (PC) |
| Colour   | Night black        |

Architecture

|                           |                 |
|---------------------------|-----------------|
| Control/operation element | Push-button/key |
|---------------------------|-----------------|

Sustainability

|              |     |
|--------------|-----|
| RoHS conform | Yes |
|--------------|-----|