



SPB340D

Surge Protection Device 3P T2 TNC Uc 275V In 20kA Imax 40kA

Technical Features

Capacity

Number of modules	3
-------------------	---

Voltage

Rated operational voltage Ue	240 - 415 V
Continuous operating voltage Uc according to IEC 61643-1	275 V
Voltage protection level Up according to IEC 61643-1	1.35 kV
Voltage protection level Up L-PE/N-PE according to IEC 61643-11	1.50 kV
Voltage level Up L-N/PEN IEC 61643-11	1350 V

Electric current

Nominal discharge current In 8 - 20 µs L-N(PEN)/N-PE IEC 61643	20 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (Imax) L-N(PEN)/ N-PE	40 kA

Dimensions

Height	89.80 mm
Width	53.40 mm
Depth	65.7 mm

Use conditions

Operating temperature	-40 - 80 °C
-----------------------	-------------

Network configuration

Network type	TN TT
--------------	----------

Equipment

With remote signalling contact	No
--------------------------------	----

Connection

Cross-section of input and output with screws, for flexible conductors	1.5 - 25.0 mm ²
Cross-section of input and output with screws, for massive conductors	1.5 - 35.0 mm ²

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3 - 3 Nm
---------------------------	----------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes