



WBMDUPB

Mechanism push dimmer trailing-edge

Technical Features

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
Material	Polycarbonate (PC)

Dimensions

Height	24 mm
Width	24 mm
Depth	51 mm

Architecture

Control/operation element	Single push button
---------------------------	--------------------

Power

Power consumption standby	0.10 W
---------------------------	--------

Lighting

Dimmable 230 V LED lamp	3 - 250 W
LED lamp power	250 W

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Capacity

Number of modules	1
-------------------	---

Texts

Dimming principle	Phase cut-off
Fuse	Short-circuit and overload-proof (electronic fuse)
Installation mode	RotoLoc®
Type of connection	With screw terminals
Extension unit input	With extension unit input for slave push-button WBMESL
Operation and control	No Bluetooth interface

Equipment

Substation input	Yes
------------------	-----

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes