



VF112TVA

Small distributor,cosmos,flush,1row,12M,IP40,MS-terminal,N+PE,transparent door

Technical Features

Installation, mounting

Mounting on Flush mounting

Electric current

Rated current 63 A

Equipment

Number of rails 2

Number of rows 1

With lock No

Has neutral terminal block Yes

Capacity

Number of modules 12

Dimensions

Height 165 mm

Width 306 mm

Depth 90.50 mm

Built-in height 165 mm

Built-in width 267 mm

Cover, door

Number of cabinet doors 1

Dimensions

Built-in depth 61 mm

Cover, door

Number of locks 0

Dimensions

Number of width units 12

Cover, door

Door/cover is transparent Yes

Materials

Material Plastic

RAL code 9010

Colour Pure white

Equipment

Has earthing terminal block Yes

Has mounting plate No

Safety

Impact resistance IK IK07

Ingress Protection (IP) class IP40

Locking type Snap on lock

Glow wire test 650 °C

Sustainability

REACH-SVHC free Yes

RoHS conform Yes