



SPL040N

Cartridge N-PE In 20kA I_{max} 40kA

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage U _e	230 - 230 V
Continuous operating voltage U _c according to IEC 61643-1	260 V
Voltage protection level U _p according to IEC 61643-1	1.90 kV
Voltage level U _p L-N/PEN IEC 61643-11	1500 V

Electric current

Nominal discharge current I _n 8 - 20 μs L-N(PEN)/N-PE IEC 61643	35 kA
Max. discharge (I _{max}) L-N(PEN)/ N-PE	65 kA

Dimensions

Height	53.5 mm
Width	18 mm
Depth	42.5 mm

Use conditions

Operating temperature	-40 - 85 °C
-----------------------	-------------

Network configuration

Network type	TN-S TT
--------------	------------

Equipment

With remote signalling contact	No
--------------------------------	----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Sustainability

REACH-SVHC free	Yes
RoHS conform	Yes