



TRM702AU



Flush mounted radio inputs battery powered

Technical Features

Settings

Supported configuration mode	ETS easy
------------------------------	-------------

Electric current

Number of entry circuits	2
--------------------------	---

Equipment

External signal voltage necessary	No
-----------------------------------	----

Connectivity

With bus system KNX radio	Yes
---------------------------	-----

Equipment

Radio frequency bidirectional	Yes
-------------------------------	-----

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Lighting

LED controlling	Yes
-----------------	-----

Materials

Colour	Light grey
--------	------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Use conditions

Operating temperature	-5 - 45 °C
-----------------------	------------

Voltage

Input voltage	3 - 3 V
Type voltage supply	DC

Dimensions

Height	30 mm
--------	-------

Texts

Installation mode	For installation behind flush-mounted inserts
Type of connection	With screw-in lift terminals

Sustainability

RoHS conform	Yes
--------------	-----