



SPN115R

SPD 1P pluggable 15kA class 2 with reserve + remote contact

Technical Features

Capacity

Number of modules	1
-------------------	---

Voltage

Rated operational voltage Ue	230 - 400 V
Continuous operating voltage U _c according to IEC 61643-1	275 V
Voltage protection level U _p according to IEC 61643-1	1 kV
Voltage protection level U _p L-PE/N-PE according to IEC 61643-11	1 kV
Type voltage supply	AC

Electric current

Nominal discharge current I _n 8 - 20 μs L-N(PEN)/N-PE IEC 61643	5 kA
Max. overcurrent protection device, parallel connection (fuse)	125 A
Max. discharge (I _{max}) L-N(PEN)/ N-PE	15 kA

Dimensions

Height	90 mm
Width	18 mm
Depth	67 mm

Use conditions

Operating temperature	-40 - 60 °C
-----------------------	-------------

Network configuration

Network type	TN-C TN-S TT
--------------	--------------------

Equipment

With remote signalling contact	Yes
--------------------------------	-----

Standards

Requirement class IEC 61643	T2
-----------------------------	----

Frequency

Frequency	50 - 60 Hz
-----------	------------

Installation, mounting

Nominal tightening torque	3.60 - 3.60 Nm
---------------------------	----------------

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes