



WGCXS113SDPKB

13A SINGLE DP SWITCHED SOCKET, KB

Technical Features

Voltage

Rated voltage	250 V
---------------	-------

Electric current

Output current	0 mA
Rated current	13 A

Voltage

Output voltage	0-0 V
----------------	-------

Use conditions

Operating temperature	-20 - 45 °C
-----------------------	-------------

Frequency

Frequency	50 - 60 Hz
-----------	------------

Power

Output power	0 W
Power consumption standby	0 W

Materials

Colour	Knight black
Surface finish	Matt
Material	Polycarbonate (PC)
Treatment	Coated
Contains recycled material (% of total plastic weight)	0 %

Dimensions

Height	16 mm
Width	86 mm
Depth	16 mm

Cable

Cable length	0 m
--------------	-----

Dimensions

Built-in depth flush-mounted boxes	35 mm
Built-in depth	16 mm

Connection

Connector/plug type	British Standard
Cross-section flexible conductor without wire end sleeve	0,08 - 4 mm ²
Number of conduit inlets	0

Installation, mounting

Mounting on	Flush mounting
Mounting-/Connection Position	Back

Connectivity

Type of connection	Screw terminal
With claw mounting	No
Mounting type	Screw mounting
Connector/plug type USB	British Standard

Equipment

Connector/plug type socket outlet	British Standard
Rotated central insert	Yes
With hinged lid	No
With round protective earth pin	No

Equipment

With signal lamp	No
With lock	No

Accessories

Has labelling field	No
Pre-equipped with	None

Capacity

Number of modules	0
-------------------	---

Safety

With enhanced contact protection	No
Impact resistance IK	IK02
Ingress Protection (IP) class	IP20

Functions

With orientation lighting	No
With function lighting	No

Identification

With imprint	No
--------------	----

Suitable for

shark

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes