



WBHP115-MB

Allure Single GPO 15A MB

**Technical Features**

**Electric current**

Rated current	15 A
---------------	------

**Frequency**

Frequency	50 - 50 Hz
-----------	------------

**Materials**

Colour	Black
--------	-------

**Installation, mounting**

Mounting on	Flush mounting
-------------	----------------

**Connectivity**

Type of connection	Screw terminal
--------------------	----------------

Mounting type	Screw mounting
---------------	----------------

**Equipment**

Connector/plug type socket outlet	Australian standard AS/NZS 3112
-----------------------------------	---------------------------------

Rotated central insert	No
------------------------	----

With hinged lid	No
-----------------	----

**Accessories**

Has labelling field	No
---------------------	----

**Capacity**

Number of modules	1
-------------------	---

**Functions**

With orientation lighting	No
---------------------------	----

With function lighting	No
------------------------	----

**Texts**

Imprint	Without imprint
---------	-----------------

Cover	Full cover plate
-------	------------------

Type of connection	With screw terminals
--------------------	----------------------

**Suitable for**

allure	
--------	--

**Sustainability**

Halogen free	Yes
--------------	-----

RoHS conform	Yes
--------------	-----