



WBHP115-MW

Allure Single GPO 15A MW

Technical Features

Electric current

Rated current	15 A
---------------	------

Voltage

Nominal voltage	250 - 250 V
-----------------	-------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
--------	-------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No

Accessories

Has labelling field	No
---------------------	----

Capacity

Number of modules	1
-------------------	---

Functions

With orientation lighting	No
With function lighting	No

Texts

Imprint	Without imprint
Cover	Full cover plate
Type of connection	With screw terminals

Suitable for

allure	
--------	--

Sustainability

Halogen free	Yes
REACH-SVHC free	Yes
RoHS conform	Yes