

fuse switch disconnecter D02 1P+N 32A

Technical Features

Fuse

Fuse size D02

Architecture

Number of poles 1

Electric current

Rated current 63 A

Installation, mounting

Mounting on DIN rail

Dimensions

Height 90 mm

Width 27 mm

Depth 64 mm

Connection

Cross-section flexible conductor 35 mm² max.

Use conditions

Operating temperature -25 - 55 °C

Frequency

Frequency 50 - 50 Hz

Power

Total power loss under IN 1.80 W

Connection

Cross-section rigid conductor 35 mm²

Materials

Material Plastic