



VB10101T

Vega 4Row 7W 1RCD - 2x6A Ltg. RCBOs

Technical Features

Installation, mounting

Mounting on	Surface mounting
-------------	------------------

Capacity

Number of modules	72
-------------------	----

Electric current

Rated current	63 A
---------------	------

Dimensions

Depth	145 mm
Height	750 mm
Width	370 mm
Number of width units	18
Thickness of sidewall	2.50 mm

Cover, door

Interlockable	Yes
Door/cover is transparent	Yes

Materials

RAL code	9010
Colour	Pure white
Material	Polystyrene (PS)

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Equipment

Number of rows	4
Number of rails	4
Extension possible	Yes

Safety

Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Protection class	Isolation class II

Sustainability

RoHS conform	Yes
--------------	-----