



WGDS213SUSBEG

13A TWIN SWITCHED SOCKET+2 USB, EG

Technical Features

Voltage

| | |
|---------------|-------|
| Rated voltage | 230 V |
|---------------|-------|

Electric current

| | |
|----------------|---------|
| Output current | 2400 mA |
| Rated current | 13 A |

Voltage

| | |
|----------------|-------|
| Output voltage | 0-0 V |
|----------------|-------|

Use conditions

| | |
|-----------------------|-------------|
| Operating temperature | -20 - 45 °C |
|-----------------------|-------------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 60 Hz |
|-----------|------------|

Power

| | |
|---------------------------|--------|
| Output power | 0 W |
| Power consumption standby | 0.15 W |

Materials

| | |
|--|--------------------|
| Colour | Gold |
| Surface finish | Matt |
| Material | Polycarbonate (PC) |
| Treatment | Coated |
| Contains recycled material (% of total plastic weight) | 0 % |

Dimensions

| | |
|--------|-------|
| Height | 20 mm |
| Width | 86 mm |
| Depth | 20 mm |

Cable

| | |
|--------------|-----|
| Cable length | 0 m |
|--------------|-----|

Dimensions

| | |
|------------------------------------|-------|
| Built-in depth flush-mounted boxes | 35 mm |
| Built-in depth | 20 mm |

Connection

| | |
|--|--------------------------|
| Connector/plug type | British Standard |
| Cross-section flexible conductor without wire end sleeve | 0.08 - 4 mm ² |
| Number of conduit inlets | 0 |

Installation, mounting

| | |
|-------------------------------|----------------|
| Mounting on | Flush mounting |
| Mounting-/Connection Position | Back |

Connectivity

| | |
|-------------------------|----------------|
| Type of connection | Screw terminal |
| With claw mounting | No |
| Mounting type | Screw mounting |
| Connector/plug type USB | AA |

Equipment

| | |
|-----------------------------------|------------------|
| Connector/plug type socket outlet | British Standard |
| Rotated central insert | No |
| With hinged lid | No |
| With round protective earth pin | No |

Equipment

| | |
|------------------|----|
| With signal lamp | No |
| With lock | No |

Accessories

| | |
|---------------------|------|
| Has labelling field | No |
| Pre-equipped with | None |

Capacity

| | |
|-------------------|---|
| Number of modules | 0 |
|-------------------|---|

Safety

| | |
|----------------------------------|------|
| With enhanced contact protection | No |
| Impact resistance IK | IK02 |
| Ingress Protection (IP) class | IP20 |

Functions

| | |
|---------------------------|----|
| With orientation lighting | No |
| With function lighting | No |

Identification

| | |
|--------------|----|
| With imprint | No |
|--------------|----|

Suitable for

shark

Sustainability

| | |
|-----------------|-----|
| REACH-SVHC free | Yes |
| RoHS conform | Yes |